

Inhoudsopgave

Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH

2

Verloopstukken

Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH

Geldig vanaf 17-3-2026

Artikel	KG per Stuks	Bruto prijs per ST
Ndl. St. Conc. Lasverloop EN10253-2 P235GH 26.9(x2.3) X 21.3(x2.0)	0,05	19,58
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 33.7(x2.6) X 21.3(x2.0)	0,09	21,74
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 33.7(x2.6) X 26.9(x2.3)	0,09	14,91
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 42.4(x2.6) X 21.3(x2.0)	0,11	33,80
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 42.4(x2.6) X 26.9(x2.3)	0,11	18,13
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 42.4(x2.6) X 30.0(x2.6)	0,11	29,15
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 42.4(x2.6) X 33.7(x2.6)	0,11	16,76
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 48.3(x2.6) X 21.3(x2.0)	0,17	55,81
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 48.3(x2.6) X 26.9(x2.3)	0,17	27,12
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 48.3(x2.6) X 33.7(x2.6)	0,17	20,45
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 48.3(x2.6) X 42.4(x2.6)	0,17	20,45
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 57(x2.9) X 33.7(x2.6)	0,26	26,75
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 57.0(x2.9) X 42.4(x2.6)	0,28	21,44
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 57.0(x2.9) X 44.5(x2.6)	0,26	21,44
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 57.0(x2.9) X 48.3(x2.6)	0,26	16,50
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 60.3(x2.9) X 21.3(x2.0)	0,26	70,75
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 60.3(x2.9) X 26.9(x2.3)	0,28	47,92
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 60.3(x2.9) X 33.7(x2.6)	0,28	31,65
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 60.3(x2.9) X 38.0(x2.6)	0,28	43,25
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 60.3(x2.9) X 42.4(x2.6)	0,28	23,26
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 60.3(x2.9) X 48.3(x2.6)	0,28	21,74
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 70(x2.9) X 57.0(x2.9)	0,39	34,08
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 76.1(x2.9) X 33.7(x2.6)	0,42	47,92
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 76.1(x2.9) X 42.4(x2.6)	0,42	39,38
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 76.1(x2.9) X 48.3(x2.6)	0,42	29,96
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 76.1(x2.9) X 57.0(x2.9)	0,42	29,76
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 76.1(x2.9) X 60.3(x2.9)	0,42	26,22
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 88.9(x3.2) X 33.7(x2.6)	0,55	87,79
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 88.9(x3.2) X 42.4(x2.6)	0,55	53,50
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 88.9(x3.2) X 44.5(x2.6)	0,55	63,60
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 88.9(x3.2) X 48.3(x2.6)	0,55	40,46
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 88.9(x3.2) X 57.0(x2.9)	0,55	38,62
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 88.9(x3.2) X 60.3(x2.9)	0,55	33,05
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 88.9(x3.2) X 70,0(x2.9)	0,55	41,07

Artikel	KG per Stuks	Bruto prijs per ST
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 88.9(x3.2) X 76.1(x2.9)	0,55	33,05
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 101.6(x3.6) X 48.3(x2.6)	0,85	96,05
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 101.6(x3.6) X 60.3(x2.9)	0,85	118,43
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 101.6(x3.6) X 76.1(x2.9)	0,85	104,97
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 101.6(x3.6) X 88.9(x3.2)	0,85	42,71
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 108.0(x3.6) X 48.3(x2.6)	0,85	91,63
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 108.0(x3.6) X 57.0(x2.9)	0,85	71,02
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 108.0(x3.6) X 60.3(x2.9)	0,85	63,70
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 108.0(x3.6) X 76.1(x2.9)	0,85	53,01
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 108.0(x3.6) X 88.9(x3.2)	0,85	54,61
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 114.3(x3.6) X 42.4(x2.6)	0,98	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 114.3(x3.6) X 48.3(x2.6)	0,98	89,00
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 114.3(x3.6) X 57.0(x2.9)	0,98	76,25
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 114.3(x3.6) X 60.3(x2.9)	0,98	50,38
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 114.3(x3.6) X 76.1(x2.9)	0,98	48,86
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 114.3(x3.6) X 88.9(x3.2)	0,98	45,91
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 114.3(x3.6) X 101.6(x3.6)	0,98	98,50
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 133(x4.0) X 57.0(x2.9)	1,61	138,57
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 133(x4.0) X 60.3(x2.9)	1,61	152,58
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 133(x4.0) X 76.1(x2.9)	1,61	101,72
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 133(x4.0) X 88.9(x3.2)	1,61	85,26
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 133(x4.0) X 108(x3.6)	1,61	86,24
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 133(x4.0) X 114.3(x3.6)	1,61	111,35
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 139.7(x4.0) X 60.3(x2.9)	1,70	164,36
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 139.7(x4.0) X 76.1(x2.9)	1,70	119,08
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 139.7(x4.0) X 88.9(x3.2)	1,70	96,44
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 139.7(x4.0) X 101.6(x3.6)	1,70	221,43
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 139.7(x4.0) X 108(x3.6)	1,70	103,90
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 139.7(x4.0) X 114.3(x3.6)	1,70	73,95
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 159(x4.5) X 57(x2.9)	2,55	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 159(x4.5) X 60.3(x2.9)	2,55	248,57
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 159(x4.5) X 76.1(x2.9)	2,39	165,61
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 159(x4.5) X 88.9(x3.2)	2,39	146,36
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 159(x4.5) X 108(x3.6)	2,39	125,59
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 159(x4.5) X 114.3(x3.6)	2,39	126,21
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 159(x4.5) X 133(x4.0)	2,39	115,20
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 159(x4.5) X 139.7(x4.0)	2,39	160,18
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 168.3(x4.5) X 60.3(x2.9)	2,55	324,56

Artikel	KG per Stuks	Bruto prijs per ST
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 168.3(x4.5) X 76.1(x2.9)	2,55	226,10
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 168.3(x4.5) X 88.9(x3.2)	2,55	176,78
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 168.3(x4.5) X 101.6(x3.6)	2,55	157,64
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 168.3(x4.5) X 108(x3.6)	2,55	176,78
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 168.3(x4.5) X 114.3(x3.6)	2,55	117,23
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 168.3(x4.5) X 133(x4.0)	3,95	158,15
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 168.3(x4.5) X 139.7(x4.0)	2,55	111,06
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 193.7(x5.6) X 114.3(x3.6)	3,95	434,47
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 193.7(x5.6) X 133(x4.0)	3,95	414,81
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 193.7(x5.6) X 139.7(x4.0)	3,95	361,76
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 193.7(x5.6) X 159(x4.5)	3,95	325,19
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 193.7(x5.6) X 168.3(x4.5)	3,95	305,80
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 219.1(x6.3) X 88.9(x3.2)	5,03	500,39
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 219.1(x6.3) X 108(x3.6)	5,03	383,16
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 219.1(x6.3) X 114.3(x3.6)	5,03	296,95
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 219.1(x6.3) X 133(x4.0)	5,03	282,54
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 219.1(x6.3) X 139.7(x4.0)	5,03	233,69
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 219.1(x6.3) X 159(x4.5)	5,03	227,47
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 219.1(x6.3) X 168.3(x4.5)	5,03	192,47
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 219.1(x6.3) X 193.7(x5.6)	5,03	379,43
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 267(x6.3) X 108(x3.6)	7,36	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 267(x6.3) X 159(x4.5)	7,36	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 267(x6.3) X 219.1(x6.3)	7,36	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 273(x6.3) X 114.3(x3.6)	7,36	512,68
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 273(x6.3) X 133(x4.0)	7,36	437,17
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 273(x6.3) X 139.7(x4.0)	7,36	397,74
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 273(x6.3) X 159(x4.5)	7,36	456,68
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 273(x6.3) X 168.3(x4.5)	7,36	323,70
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 273(x6.3) X 193.7(x5.6)	7,36	593,88
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 273(x6.3) X 219.1(x6.3)	7,36	282,28
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 323.9(x7.1) X 139.7(x4)	0,10	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 323.9(x7.1) X 159(x4.5)	11,30	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 323.9(x7.1) X 168.3(x4.5)	11,30	654,38
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 323.9(x7.1) X 193.7(x5.6)	11,30	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 323.9(x7.1) X 219.1(x6.3)	11,30	582,89
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 323.9(x7.1) X 273(x6.3)	11,30	502,24
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 355.6(x8.0) X 168.3(x4.5)	22,50	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 355.6(x8.0) X 219.1(x6.3)	22,50	1.668,58

Artikel	KG per Stuks	Bruto prijs per ST
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 355.6(x8.0) X 273(x6.3)	22,50	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 355.6(x8.0) X 323.9(x7.1)	22,50	1.315,72
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 406.4(x8.8) X 219.1(x6.3)	30,50	3.563,32
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 406.4(x8.8) X 273(x6.3)	30,60	2.900,34
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 406.4(x8.8) X 323.9(x7.1)	30,60	2.379,95
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 406.4(x8.8) X 355.6(x8.0)	30,60	2.434,94
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 508(x11.0) X 323.9(x7.1)	68,50	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 508(x11.0) X 355.6(x8)	68,50	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 508(x11.0) X 406,4(x8.8)	68,50	3.646,26
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 610(x12,5) X 323.9(x7.1)	79,00	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 610(x12,5) X 457(x10)	79,00	*
Ndl. st. concentrisch. lasverloop EN10253-2 - P235GH 610(x12,5) X 508(x11)	79,00	*